



3) Threaded pin, 4) not included in scope of delivery, 5) Female, removable, 6) Allen key size 2

Basic features

| | |
|--------------------------|------------------------------|
| Scope of delivery | Protective cap |
| Short description | Protective ring |
| Use | for inductive sensors BES M8 |

Environmental conditions

| | |
|----------------------------|--------------|
| Ambient temperature | -50...650 °C |
|----------------------------|--------------|

Material

| | |
|-------------------------|--------------------------|
| Housing material | Stainless steel |
| Material | Stainless steel (1.4401) |

Mechanical data

| | |
|-------------------------|--------------------|
| Clamping system | Screws |
| Diameter 2 | 8.00 mm |
| Dimension | Ø 15 x 8 mm |
| Installation | for flush mounting |
| Mounting | Screws |
| Size | M8x1 |
| Wall thickness t | 3.5 mm |