


## Recommended Land Pattern

- An example of a land pattern for the Rectangular Type is shown below.




| Size<br>mm/inch | Dimensions (mm) |            |              |
|-----------------|-----------------|------------|--------------|
|                 | a               | b          | c            |
| 0402/01005      | 0.15 to 0.20    | 0.5 to 0.7 | 0.20 to 0.25 |
| 0603/0201       | 0.3 to 0.4      | 0.8 to 0.9 | 0.25 to 0.35 |
| 1005/0402       | 0.5 to 0.6      | 1.4 to 1.6 | 0.4 to 0.6   |
| 1608/0603       | 0.7 to 0.9      | 2.0 to 2.2 | 0.8 to 1.0   |
| 2012/0805       | 1.0 to 1.4      | 3.2 to 3.8 | 0.9 to 1.4   |
| 3216/1206       | 2.0 to 2.4      | 4.4 to 5.0 | 1.2 to 1.8   |
| 3225/1210       | 2.0 to 2.4      | 4.4 to 5.0 | 1.8 to 2.8   |
| 4532/1812       | 3.3 to 3.7      | 5.7 to 6.5 | 2.3 to 3.5   |
| 5025/2010       | 3.6 to 4.0      | 6.2 to 7.0 | 1.8 to 2.8   |
| 6432/2512       | 5.0 to 5.4      | 7.6 to 8.6 | 2.3 to 3.5   |
| 6432/2512*      | 3.6 to 4.0      | 7.6 to 8.6 | 2.3 to 3.5   |

High power (double-sided resistive elements structure) type

| Part No.                | Size<br>mm/inch | Dimensions (mm) |            |            |
|-------------------------|-----------------|-----------------|------------|------------|
|                         |                 | a               | b          | c          |
| ERJ2LW/2BW              | 1005/0402       | 0.52            | 1.4 to 1.6 | 0.4 to 0.6 |
| ERJ3LW/3BW              | 1608/0603       | 0.5 to 0.8      | 2.5 to 2.7 | 0.9 to 1.1 |
| ERJ6LW                  | 2012/0805       | 0.6 to 0.8      | 3.2 to 3.8 | 1.1 to 1.4 |
| ERJ6BW                  | 2012/0805       | 0.9             | 3.2 to 3.8 | 1.1 to 1.4 |
| ERJ6CW<br>(10 to 13 mΩ) | 2012/0805       | 0.7 to 0.9      | 3.2 to 3.8 | 1.1 to 1.4 |
| ERJ6CW<br>(15 to 30 mΩ) | 2012/0805       | 0.9 to 1.1      | 3.2 to 3.8 | 1.1 to 1.4 |
| ERJ8BW                  | 3216/1206       | 1.2             | 4.4 to 5.0 | 1.3 to 1.8 |
| ERJ8CW<br>(10 to 16 mΩ) |                 |                 |            |            |
| ERJ8CW<br>(18 to 50 mΩ) | 3216/1206       | 2.0 to 2.6      | 4.4 to 5.0 | 1.2 to 1.8 |

\* ERJL1W



- An example of a land pattern for High Power Chip Resistors / Wide Terminal Type is shown below.



| Part No.                                              | Dimensions (mm) |      |      |
|-------------------------------------------------------|-----------------|------|------|
|                                                       | a               | b    | c    |
| ERJA1                                                 | 6.4             | 1.70 | 0.60 |
| ERJB1<br>ERJC1 <sup>(1)</sup><br>ERJD1 <sup>(2)</sup> | 5.0             | 1.30 | 0.75 |
| ERJB2<br>ERJD2 <sup>(2)</sup>                         | 3.2             | 0.95 | 0.70 |
| ERJB3                                                 | 2.0             | 0.80 | 0.60 |



- (1) Anti-Sulfurated High Power Chip Resistors / Wide Terminal Type  
 (2) Low TCR High Power Chip Resistors / Wide Terminal Type

● An example of a land pattern for Chip Resistor Array, Anti-Sulfurated Chip Resistor Array and Chip Attenuator is shown below.



| Part No.                   | Dimensions (mm) |              |      |              |
|----------------------------|-----------------|--------------|------|--------------|
|                            | a               | b            | c    | d            |
| EXB14V<br>EXB14A           | 0.30            | 0.30         | 0.30 | 0.80 to 0.90 |
| EXB24V<br>EXBU24<br>EXB24A | 0.5             | 0.35 to 0.40 | 0.30 | 1.4 to 1.5   |

| Part No.                 | Dimensions (mm) |              |              |              |      |
|--------------------------|-----------------|--------------|--------------|--------------|------|
|                          | a               | b            | c            | f            | P    |
| EXB18V                   | 0.20 to 0.30    | 0.15 to 0.20 | 0.15 to 0.20 | 0.80 to 0.90 | 0.40 |
| EXBV4V,V8V               | 0.7 to 0.9      | 0.4 to 0.45  | 0.4 to 0.45  | 2 to 2.4     | 0.80 |
| EXB34V,38V<br>EXBU34,U38 | 0.7 to 0.9      | 0.4 to 0.5   | 0.4 to 0.5   | 2.2 to 2.6   | 0.80 |
| EXBS8V                   | 1 to 1.2        | 0.5 to 0.75  | 0.5 to 0.75  | 3.2 to 3.8   | 1.27 |



| Part No.         | Dimensions (mm) |              |      |      |              |
|------------------|-----------------|--------------|------|------|--------------|
|                  | a               | b            | c    | d    | f            |
| EXB28V<br>EXBU28 | 0.40            | 0.525        | 0.25 | 0.25 | 1.40         |
| EXBN8V           | 0.45 to 0.50    | 0.35 to 0.38 | 0.25 | 0.25 | 1.40 to 2.00 |

| Part No.         | Dimensions (mm) |       |      |      |      |
|------------------|-----------------|-------|------|------|------|
|                  | a               | b     | c    | d    | f    |
| EXB2HV<br>EXBU2H | 1.00            | 0.425 | 0.25 | 0.25 | 2.00 |

● An example of a land pattern for Chip Resistor Networks is shown below.

|                           | EXBA                                                        | EXBE                                  |
|---------------------------|-------------------------------------------------------------|---------------------------------------|
| For popular pattern       | Pitch 1.27 mm<br>                                           | Pitch 0.8 mm<br>                      |
| For high density pattern* | Pitch 0.635 mm<br>Through-hole less<br>EXBA10P, EXBA10E<br> | Pitch 0.4 mm<br>Through-hole less<br> |
| For popular pattern       | Pitch 0.635 mm<br>                                          | Pitch 0.5 mm<br>                      |

\* When designing high density land patterns, examine the reliability of isolation among the lines and adopt the chip resistor networks.