


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
	A	INITIAL RELEASE	01JUN2011	RC	AH		



ASSEMBLY CONNECTIVITY	
LC CONN.	LC CONN.
YELLOW (A)	WHITE (B)
WHITE (B)	YELLOW (A)

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061528-Y	XY.0

NOTES:

- ATTENUATION ≤ 0.3 dB, MEASURED AT 850 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
 - RETURN LOSS ≥ 20 dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 850 nm
 - FILLED OUT TEST RESULT SHEET SUPPLIED WITH EACH INDIVIDUALLY PACKED ASSEMBLY
 - CABLE INFORMATION:
 - CORE DIAMETER: 62.5/125 μ m (2x)
 - OUTER JACKET DIAMETER: 1.8 x 3.6 mm
 - OUTER JACKET COLOUR: GREY
 - OUTER JACKET MATERIAL: LSZH
- BLANK LABEL
 ONLY ONE LABEL IN THE MIDDLE OF THE CABLE IS USED FOR LENGTHS < 0.6 METER

2	BLANK LABEL	3
2	LC DUPLEX CONNECTOR, ULTRA SHORT, MULTI MODE, BEIGE	2
L	FOCAB 1.8MZ 62.5/125, GREY, LSZH	1
Qty	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 13APR2011		
DIMENSIONS: mm		CHK R. GROENEVELD 01JUN2011		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 01JUN2011	NAME	
0 PLC ± 1.0		PRODUCT SPEC	FIBER OPTIC LEAD 1.8MZ	
1 PLC ± 0.5		APPLICATION SPEC	LC/DPX - LC/DPX ULTRA SHORT	
2 PLC $\pm -$		WEIGHT	SIZE	RESTRICTED TO
3 PLC $\pm -$		SCALE	CAGE CODE	DRAWING NO
4 PLC $\pm -$		CUSTOMER DRAWING	00779	C=2061528
ANGLES $\pm -$		FINISH	SCALE	SHEET
FINISH		SCALE	NTS	1 of 1
MATERIAL		REV	A	