

Basic features

Application	Ethernet, CAT 5
Approval/Conformity	CE EAC WEEE

Electrical connection

Bending radius min., flexible cable	10 x D
Cable	TPE Shielded Red, 25.00 m, Drag chain compatible
Cable diameter D	6.10 mm ±0.25 mm
Cable, bending cycles min.	10 million
Cable, note	Ethernet, CAT 5E
Conductor cross-section	24 AWG
Connection 1	RJ45-Male, straight, 4-pin
Connection 2	RJ45-Male, straight, 4-pin
Number of conductors	4
System	assembled/assembled

Electrical data

Cable rated voltage AC max.	600 V
Cable rated voltage DC max.	600 V
Conductor construction	2x2 twisted-pair
Conductor resistance	≤ 26.0 Ohm/1000 ft
Coupling resistance max.	100 Ohm ±15 Ohm
Operating capacitance	13.5 pF/ft
Operating voltage U _b	42 VDC / 30 VAC
Rated current (40 °C)	1.0 A
Transfer rate	10...100 Mbit/s

Environmental conditions

Cable temperature, flexible routing	-40...80 °C
Protection degree	IP20/IP20

Material

Cable jacket material, note	Shielded
Cable jacket, material	TPE
Cable shield	Aluminum foil and copper braid
Material contact carrier	PBT/PBT
Material contacts	Phosphor bronze, gold plated/ Phosphor bronze, gold plated
Material grip	PVC/PVC


Mechanical data

Cable jacket, color	Red
Cable length L	25.00 m
Cable properties	Drag chain compatible

Remarks

Cable construction acc. to UL CMX Outdoor or AWM Style 2463
Enclosure rating per IEC 60529 or ISO 20653, only in screwed state with the associated mating piece.

Connector Drawings



1.....8

I , II

PIN 1: white/orange

PIN 2: orange

PIN 3: white/green

PIN 4: n.c.


PIN 5: n.c.

PIN 6: green

PIN 7: n.c.

PIN 8: n.c.

Wiring Diagrams



1) Shield on housing