


## Double-Ended Cordsets

**BCC S4B8-S4B8-3A-321-YX8825-050-C009**

**Order Code: BCC0JW5**

# BALLUFF



### Basic features

Approval/Conformity	FDA compliant
	CE
	EAC
	Ecolab
	WEEE

### Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	TPE-V gray, 5 m
Cable diameter D	6.0 mm ±0.2 mm
Conductor cross-section	0.25 mm <sup>2</sup>
Connection 1	M12x1-Female, straight, 8-pin, A-coded
Connection 2	M12x1-Male, straight, 8-pin, A-coded
Number of conductors	8
System	Molded/Molded

### Electrical data

Cable rated voltage AC max.	300 V
Cable rated voltage DC max.	300 V
Operating voltage U <sub>b</sub>	30 VDC / 30 VAC
Rated current (40 °C)	2.0 A

### Environmental conditions

Cable temperature, fixed routing	-50...105 °C
Cable temperature, flexible routing	-25...105 °C
Protection degree	IP67, IP69K/IP67, IP69K

### Material

Cable jacket, material	TPE-V
Material contact carrier	PP/PP
Material contacts	Bronze/Brass
Material cover nut	Stainless steel (1.4404)/Stainless steel (1.4404)
Material grip	PP/PP

### Mechanical data

Cable jacket, color	gray
Cable length L	5.00 m
Tightening torque pigtail	0.6 Nm/0.6 Nm

### Remarks


Halogen-free per DIN VDE 0472 Part 815

Halogen-free acc. to IEC 60754-1


LABS-free

Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

**Connector Drawings**



- II
- PIN 1: brown
  - PIN 2: white
  - PIN 3: blue
  - PIN 4: black
  - PIN 5: gray
  - PIN 6: pink
  - PIN 7: purple
  - PIN 8: orange



- I
- PIN 1: brown
  - PIN 2: white
  - PIN 3: blue
  - PIN 4: black
  - PIN 5: gray
  - PIN 6: pink
  - PIN 7: purple
  - PIN 8: orange

**Wiring Diagrams**

