

### Basic features

Approval/Conformity	CE
	EAC
	WEEE

### Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 2.00 m, Drag chain compatible
Cable diameter D	4.60 mm ±0.20 mm
Cable, bending cycles min.	2 million
Conductor cross-section	0.50 mm <sup>2</sup>
Connection	A, DIN-0°/180°-Valve connector, right-angle, 4-pin
Connector configuration	right-angle
Number of conductors	3
Number of pins	4
System	Molded

### Electrical data

Operating voltage $U_b$	24 VDC / 24 VAC
Rated current (40 °C)	6.0 A
Suppressor	Suppressor diode

### Environmental conditions

Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...80 °C
Cable temperature, flexible routing	-25...80 °C
Protection degree	IP67

### Material

Cable jacket, material	PUR
Material contact carrier	PA 6.6
Material contacts	Brass
Material grip	TPU
Material locking screw	Steel

Single-Ended Cordsets  
**BCC VA04-0000-10-053-PX0350-020**  
Order Code: BCC04W0

# BALLUFF

## Mechanical data


Acceleration max., drag chain	5 m/s <sup>2</sup>
Cable jacket, color	black
Cable length L	2.00 m
Cable properties	Drag chain compatible

Horizontal travel permitted, drag chain	5 m
Tightening torque pigtail	0.5 Nm
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	2 m

## Remarks

Cable construction acc. to UL-AWM Style 20549  
Halogen-free acc. to EN 50267-2-1  
Silicone-free  
Flame resistance per IEC 60332-2-2  
\* style A per EN 175301-803  
Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## Connector Drawings



PIN 1: brown

PIN 2: blue

PIN PE: green/yellow

## Wiring Diagrams

