

Basic features

Approval/Conformity	CE EAC WEEE
---------------------	-------------------

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PUR black, 5.00 m, Drag chain compatible
Cable diameter D	4.60 mm ±0.20 mm
Cable, bending cycles min.	2 million
Conductor cross-section	0.50 mm ²
Connection	B, Ind.-0°-Valve connector, right-angle, 3-pin
Connector configuration	right-angle
Number of conductors	3
Number of pins	3
System	Molded

Electrical data

Operating voltage U _b	24 VDC / 24 VAC
Rated current (40 °C)	4.0 A
Suppressor	Suppressor diode

Environmental conditions

Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...80 °C
Cable temperature, flexible routing	-25...80 °C
Protection degree	IP67

Material

Cable jacket, material	PUR
Material contact carrier	PBT
Material contacts	Brass
Material grip	TPU
Material locking screw	Steel

Single-Ended Cordsets
BCC VB43-0000-10-055-PX0350-050
Order Code: BCC03YM

BALLUFF

Mechanical data


Acceleration max., drag chain	5 m/s ²
Cable jacket, color	black
Cable length L	5.00 m
Cable properties	Drag chain compatible

Horizontal travel permitted, drag chain	5 m
Tightening torque pigtail	0.5 Nm
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	2 m

Remarks

Cable construction acc. to UL-AWM Style 20549
Halogen-free acc. to EN 50267-2-1
Silicone-free
Flame resistance per IEC 60332-2-2
* style B industry standard
Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

Connector Drawings



PIN 1: brown

PIN 2: blue

PIN PE: green/yellow

Wiring Diagrams

