

1) Sensing surface, 2) Housing, 3) Cover, 4) Potentiometer, 5) NO or NC selectable, 6) LED function indicator



IND. CONT. EQ
 81U2
 for use in the secondary of
 a class 2 source of supply

Basic features

Approval/Conformity	CE cULus WEEE
Basic standard	IEC 60947-5-2
Scope of delivery	Nut (2x)
Sensitivity	Switching distance adjustable
Series	M30

Display/Operation

Function indicator	yes
Power indicator	yes

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Operating voltage U_b	10...35 VDC
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	300 mA
Ripple max. (% of U_e)	10 %
Switching frequency	100 Hz
Utilization category	DC -13
Voltage drop static max.	1.8 V

Environmental conditions

Ambient temperature	-30...70 °C
Protection degree	IP66 IP64 at plug exit

Functional safety

MTTF (40 °C)	455 a
--------------	-------

Material

Cover material	PBT PE
Housing material	Stainless steel (1.4301)
Material sensing surface	PTFE

Mechanical data

Dimension	Ø 30 x 86.5 mm
Installation	non-flush
Size	M30x1.5
Thread (A)	M30x1.5
Tightening torque	90 Nm

Output/Interface

Switching output	PNP NO/NC programmable
------------------	------------------------

Capacitive Sensors
BCS M30T4M2-PPC30G-S04G
Order Code: BCS007L


BALLUFF

Range/Distance

Hysteresis H max. (% of Sr) 15.0 %
Measuring range 1...30 mm

Rated operating distance S_n 30 mm
Repeat accuracy max. (% of Sr) 5.0 %
Temperature drift max. (% of Sr) 15 %

Connector Drawings



Wiring Diagrams

