

Basic features

Approval/Conformity	CE EAC WEEE
---------------------	-------------------

Display/Operation

Power indicator	no/no
-----------------	-------

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	15 x D
Cable	PUR Shielded Green, 5.00 m
Cable diameter D	6.70 mm ±0.20 mm
Cable, bending cycles min.	2 million
Conductor cross-section	0.34 mm ²
Connection 1	M12x1-Female, straight, 4-pin, D-coded
Connection 2	RJ45-Male, straight, 4-pin
Connector 01, version	Straight
Connector 02, version	Straight
Number of conductors	4
System	Molded/Molded

Electrical data

Operating voltage U _b	60 VDC / 60 VAC
----------------------------------	-----------------

Environmental conditions

Cable temperature, drag chain	-20...60 °C
Cable temperature, flexible routing	-20...60 °C
Protection degree	IP67/IP20

Material

Cable jacket material, note	Shielded
Cable jacket, material	PUR
Material contact carrier	PUR/PUR
Material contacts	Brass/Brass
Material grip	PUR/PUR


Mechanical data

Acceleration max., drag chain	2 m/s ²
Cable jacket, color	Green
Cable length L	5.00 m
Horizontal travel permitted, drag chain	5 m at 5 m/s ²
Mounting	PG9
Traverse speed max., drag chain	200 m/min
Vertical travel permitted, drag chain	5 m at 5 m/s ²

Remarks

Halogen-free

Connector Drawings



Wiring Diagrams

