



1) O-Ring with thrust ring



Basic features

Approval/Conformity	CE EAC WEEE
Basic standard	IEC 60947-5-2
Thrust ring, part number	505953

Display/Operation

Function indicator	no
Power indicator	no

Electrical connection

Cable diameter D	4.60 mm
Cable length L	5 m
Conductor cross-section	0.34 mm ²
Connection	M12x1-Male, 4-pin, A-coded
Connection type	Connector, 5.00 m, PUR
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U _e	0.5 μF
Min. operating current I _m	0 mA
No-load current I _o max., damped	10 mA
No-load current I _o max., undamped	1 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	33.0 kOhm + D
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	10 ms
Residual current I _r max.	10 μA
Ripple max. (% of U _e)	15 %
Switching frequency	1000 Hz
Utilization category	DC -13
Voltage drop static max.	1.5 V

Environmental conditions

Ambient temperature	-25...80 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP68

Functional safety

MTTF (40 °C)	720 a
--------------	-------

Inductive Sensors
BES 516-300-S152-S4-D
Order Code: BHS001W



Material

Gasket, material	NBR 60-80
Housing material	Stainless steel (1.4104)
Material jacket	PUR
Material sensing surface	EP
Support ring material	PTFE

Mechanical data

Dimension	Ø 16 x 73 mm
Installation	for flush mounting
Mounting	M16x1
Pressure rating max.	350 bar
Pressure rating, note	oil pressure rated
Sealing ring, part number	703843
Sealing ring, size	11 x 1.8 mm
Size	M16x1
Tightening torque	40 Nm ±10 %

Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Range/Distance

Assured operating distance Sa	1.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	1.5 mm
Real switching distance sr	1.5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

Installation Instructions 614804

The sensor is functional again after the overload has been eliminated.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

