



1) Sensing surface



IND. CONT. EQ.  
 81U2  
 Class 2 Type 1



### Basic features

Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2

### Display/Operation

Function indicator	yes
Power indicator	no

### Electrical connection

Connection	M8x1-Male, 3-pin
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at Ue	1 µF
Min. operating current I <sub>m</sub>	0 mA
No-load current I <sub>o</sub> max., damped	6 mA
No-load current I <sub>o</sub> max., undamped	2 mA
Operating voltage U <sub>b</sub>	10...30 VDC
Output resistance R <sub>a</sub>	Open drain
Rated insulation voltage U <sub>i</sub>	75 V DC
Rated operating current I <sub>e</sub>	100 mA
Rated operating voltage U <sub>e</sub> DC	24 V
Rated short circuit current	100 A
Ready delay t <sub>v</sub> max.	21 ms
Residual current I <sub>r</sub> max.	10 µA
Ripple max. (% of U <sub>e</sub> )	10 %
Switching frequency	5000 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

### Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

### Functional safety

MTTF (40 °C)	305 a
--------------	-------

Inductive Sensors  
**BES 516-3006-G-E5-C-S49**  
 Order Code: BES00HP



**Material**

Housing material	Stainless steel
Material sensing surface	PBT

**Mechanical data**

Dimension	Ø 5 x 41 mm
Installation	for flush mounting
Size	M5x0.5
Tightening torque	1 Nm

**Output/Interface**

Switching output	NPN normally open (NO)
------------------	------------------------

**Range/Distance**

Assured operating distance Sa	1.21 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	1.5 mm
Real switching distance sr	1.5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

**Remarks**

The sensor is functional again after the overload has been eliminated.  
 EMC: Surge resistance  
 External protection circuit is required. Document 825345, Section 2.  
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

