

### Basic features

Approval/Conformity	CE EAC WEEE
---------------------	-------------------

### Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable	PVC gray, 0.30 m
Cable diameter D	5.00 mm ±0.20 mm
Conductor cross-section	0.50 mm <sup>2</sup>
Connection 1	B, Ind.-0°-Female, angled, 3-pin
Connection 2	M12x1-Male, straight, 3-pin, A-coded
Number of conductors	3
System	Molded/Molded

### Electrical data

Operating voltage U <sub>b</sub>	24 VDC / 24 VAC
Rated current (40 °C)	4.0 A
Suppressor	Suppressor diode

### Environmental conditions

Cable temperature, fixed routing	-40...105 °C
Cable temperature, flexible routing	5...105 °C
Protection degree	IP67/IP67, IP69K

### Material

Cable jacket, material	PVC
Material contact carrier	PBT/TPU
Material contacts	Brass/Bronze
Material cover nut	Brass nickel plated
Material grip	PUR/PUR
Material locking screw	Steel


### Mechanical data

Cable jacket, color	gray
Cable length L	0.30 m
Tightening torque pigtail	0.5 Nm/0.6 Nm


**Remarks**

Oil resistant per DIN EN 60811-404 (VDE 0473-811-404)  
 Flame resistance per IEC 60332-1-2  
 \* style B industry standard  
 Enclosure rating per IEC 60529 or 20653, only in screwed state with the associated mating piece.

**Connector Drawings**



II  
 PIN 3: blue  
 PIN 4: brown  
 PIN 5: green/yellow



I  
 PIN 1: brown  
 PIN 2: blue  
 PIN PE: green/yellow

**Wiring Diagrams**

