



1) Sensing surface



Basic features

Approval/Conformity	CE EAC WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	1 µF
Min. operating current I _m	0 mA
No-load current I _o max., damped	25 mA
No-load current I _o max., undamped	15 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	2.0 kOhm + D + LED
Protection class	II
Rated insulation voltage U _i	250 V AC
Rated operating current I _e	130 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	10 ms
Residual current I _r max.	80 µA
Ripple max. (% of U _e)	15 %
Switching frequency	500 Hz
Utilization category	DC -13
Voltage drop static max.	3.5 V

Inductive Sensors
BES 516-346-H2-Y
Order Code: **BES01FC**

BALLUFF

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

Functional safety

MTTF (40 °C)	1620 a
--------------	--------

Material

Housing material	Aluminum
Material sensing surface	PA 12

Mechanical data

Connection cross-section	2.5 mm ²
Dimension	42 x 22 x 48 mm
Installation	for flush mounting
Tightening torque	3...4 Nm (M16x1.5)
Tightening torque clamping screw	0.4 Nm

Output/Interface

Cable fitting, thread size	M16x1.5
Switching output	PNP normally open (NO)

Range/Distance

Assured operating distance Sa	4 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	5 mm
Real switching distance sr	5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

The sensor is functional again after the overload has been eliminated.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

