



IND. CONT. EQ.
 81U2
 Class 2 Type 1



Basic features

| | |
|---------------------|----------------------------|
| Approval/Conformity | CE cULus EAC WEEE |
| Basic standard | IEC 60947-5-2 |

Display/Operation

| | |
|--------------------|-----|
| Function indicator | yes |
| Power indicator | no |

Electrical connection

| | |
|-----------------------------------|----------------------|
| Cable diameter D | 4.60 mm |
| Cable length L | 3 m |
| Conductor cross-section | 0.34 mm ² |
| Connection type | Cable, 3.00 m, PVC |
| Number of conductors | 3 |
| Polarity reversal protected | yes |
| Protection against device mix-ups | yes |
| Short-circuit protection | yes |

Electrical data

| | |
|---|--------------------|
| Load capacitance max. at U _e | 1 µF |
| Min. operating current I _m | 0 mA |
| No-load current I _o max., damped | 25 mA |
| No-load current I _o max., undamped | 15 mA |
| Operating voltage U _b | 10...30 VDC |
| Output resistance R _a | 2.0 kOhm + D + LED |
| Rated insulation voltage U _i | 75 V DC |
| Rated operating current I _e | 130 mA |
| Rated operating voltage U _e DC | 24 V |
| Rated short circuit current | 100 A |
| Ready delay t _v max. | 10 ms |
| Residual current I _r max. | 80 µA |
| Ripple max. (% of U _e) | 15 % |
| Switching frequency | 100 Hz |
| Utilization category | DC -13 |
| Voltage drop static max. | 3.5 V |

Environmental conditions

| | |
|-------------------------|---------------------------------|
| Ambient temperature | -25...70 °C |
| Contamination scale | 3 |
| EN 60068-2-27, Shock | Half-sinus, 30 gn, 11 ms |
| EN 60068-2-6, Vibration | 55 Hz, amplitude 1 mm, 3x30 min |
| Protection degree | IP68 |

Functional safety

| | |
|--------------|--------|
| MTTF (40 °C) | 1620 a |
|--------------|--------|

Inductive Sensors
BES 516-362-E4-Y-03
Order Code: BES00WW

BALLUFF

Material

| | |
|--------------------------|----------------------|
| Housing material | Brass, nickel plated |
| Material jacket | PVC |
| Material sensing surface | PA 12 |
| Surface protection | nickel plated |

Mechanical data

| | |
|-------------------|----------------|
| Dimension | Ø 30 x 48.5 mm |
| Installation | non-flush |
| Size | M30x1.5 |
| Tightening torque | 70 Nm |

Output/Interface

| | |
|------------------|------------------------|
| Switching output | PNP normally open (NO) |
|------------------|------------------------|

Range/Distance

| | |
|----------------------------------|---------|
| Assured operating distance Sa | 12.2 mm |
| Hysteresis H max. (% of Sr) | 15.0 % |
| Rated operating distance Sn | 15 mm |
| Real switching distance sr | 15 mm |
| Repeat accuracy max. (% of Sr) | 5.0 % |
| Temperature drift max. (% of Sr) | 10 % |
| Tolerance Sr | ±10 % |

Remarks

The sensor is functional again after the overload has been eliminated.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

