



### Basic features

|                               |  |
|-------------------------------|--|
| <b>Additional features</b>    | Weld immune  |
| <b>Principle of operation</b> | Clamp holder   |
| <b>Scope of delivery</b>      | Clamp holder (1x)<br>Nut DIN 1763-M12x1 (2x)                             |
| <b>Use</b>                    | for sensors Ø8 mm<br>For M08 sensors<br>fastening length 32mm and longer |

### Material

|                           |             |
|---------------------------|-------------|
| <b>Material</b>           | Brass       |
| <b>Surface protection</b> | PTFE coated |

### Mechanical data

|   |                |
|---|----------------|
| <b>Dimension</b>                        | Ø 17 x 32 mm   |
| <b>Mounting</b>                         | Screws, clamps |
| <b>Tightening torque</b>                | 10 Nm          |
| <b>Tightening torque clamping screw</b> | 1 Nm           |

### Remarks

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using the compression screw.  
 The fixed stop may alter the switching distance of the proximity switch.  
 The holder is suitable for use in welding environments.