



1) Sensing surface



Basic features

Approval/Conformity	CE
	EAC
	WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	0.15 µF
Min. operating current Im	0 mA
No-load current Io max., damped	10 mA
No-load current Io max., undamped	10 mA
Operating voltage Ub	10...30 VDC
Output resistance Ra	Open collector
Rated insulation voltage Ui	75 V DC
Rated operating current Ie	200 mA
Rated operating voltage Ue DC	24 V
Rated short circuit current	100 A
Ripple max. (% of Ue)	15 %
Switching frequency	50 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP65

Functional safety

MTTF (40 °C)	1465 a
--------------	--------

Inductive Sensors
BES IKU-011-P-1-S-S4-SA1
Order Code: BES02TC



Material

Housing material	Plastic
Material sensing surface	Plastic

Mechanical data

Dimension	100 x 35 x 35 mm
Installation	non-flush

Range/Distance

Assured operating distance Sa	24 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	30 mm
Real switching distance sr	30 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Remarks

After eliminating the overload, the sensor is functional again after a load-dependent delay time of 5-30 s.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

