



### Basic features

<b>Additional features</b>	Weld immune
<b>Application</b>	Assembly
<b>Principle of operation</b>	Clamp holder
<b>Scope of delivery</b>	Clamp holder (1x) Nut DIN 1763-M16x1 (2x)
<b>Use</b>	for sensors Ø12 mm For M12 sensors fastening length 36mm and longer
<b>Version</b>	Prox fastening

### Material

<b>Housing material</b>	Steel, PTFE coated
<b>Housing material, surface protection</b>	PTFE coated
<b>Material</b>	Steel
<b>Surface protection</b>	PTFE coated

### Mechanical data

<b>Dimension</b>	Ø 22 x 37 mm
<b>Installation</b>	for flush mounting
<b>Mounting</b>	Screws, clamps
<b>Size</b>	M12x1
<b>Tightening torque</b>	20 Nm

### Remarks

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using the compression screw.  
 The fixed stop may alter the switching distance of the proximity switch.  
 The holder is suitable for use in welding environments.  
 Not suitable for sensors with plastic housing.