



### Basic features

<b>Principle of operation</b>	Clamp holder
<b>Scope of delivery</b>	Clamp holder (1x) Nut DIN 1763-M24x1.5 (2x)
<b>Use</b>	for sensors Ø18 mm For M18 sensors fastening length 50mm and longer

### Material

<b>Material</b>	Brass
<b>Surface protection</b>	nickel plated

### Mechanical data

<b>Dimension</b>	Ø 30 x 58 mm
<b>Mounting</b>	Screws, clamps
<b>Tightening torque</b>	25 Nm
<b>Tightening torque clamping screw</b>	4 Nm

### Remarks

The proximity switch is inserted into the clamp holder up to the fixed stop and secured using the compression screw.  
 The fixed stop may alter the switching distance of the proximity switch.