



### Basic features

Approval/Conformity	CE EAC cULus WEEE
---------------------	----------------------------

### Electrical connection

Cable diameter D	3.00 mm
Cable length L	2 m
Connection type	Cable, 2.00 m, PVC
Number of conductors	3

### Electrical data

No-load current $I_0$ max., damped	7 mA
No-load current $I_0$ max., undamped	2 mA
Operating voltage $U_b$	10...30 VDC
Output resistance $R_a$	33.0 kOhm
Protection class	II
Rated insulation voltage $U_i$	250 V AC
Ready delay $t_v$ max.	25 ms
Residual current $I_r$ max.	10 $\mu$ A
Ripple max. (% of $U_e$ )	10 %
Switching frequency	5000 Hz
Voltage drop static max.	2.5 V

### Environmental conditions

Ambient temperature	-25...70 °C
Protection degree	IP68

### Functional safety

MTTF (40 °C)	595 a
--------------	-------

### Material

Housing material	Brass, Nickel-free coated
Material jacket	PVC
Material sensing surface	PBT
Surface protection	Nickel-free coated

### Mechanical data

Dimension	$\varnothing$ 8 x 50 mm
Installation	for flush mounting
Size	M8x1

### Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

### Range/Distance

Assured operating distance $S_a$	1.2 mm
Rated operating distance $S_n$	1.5 mm
Real switching distance $s_r$	1.5 mm
Switching distance marking	■

## Wiring Diagrams

