



1) Sensing surface



**Basic features**

<b>Approval/Conformity</b>	CE EAC cULus WEEE
<b>Basic standard</b>	IEC 60947-5-2

**Display/Operation**

<b>Function indicator</b>	yes
<b>Power indicator</b>	no

**Electrical connection**

<b>Cable diameter D</b>	4.60 mm
<b>Cable length L</b>	5 m
<b>Conductor cross-section</b>	0.34 mm <sup>2</sup>
<b>Connection type</b>	Cable, 5.00 m, PVC
<b>Number of conductors</b>	3
<b>Polarity reversal protected</b>	yes
<b>Protection against device mix-ups</b>	yes
<b>Short-circuit protection</b>	yes

**Electrical data**

<b>Load capacitance max. at Ue</b>	1 µF
<b>Min. operating current I<sub>m</sub></b>	0 mA
<b>No-load current I<sub>o</sub> max., damped</b>	5 mA
<b>No-load current I<sub>o</sub> max., undamped</b>	2 mA
<b>Operating voltage U<sub>b</sub></b>	10...30 VDC
<b>Output resistance R<sub>a</sub></b>	33.0 kOhm + D
<b>Protection class</b>	II
<b>Rated insulation voltage U<sub>i</sub></b>	250 V AC
<b>Rated operating current I<sub>e</sub></b>	200 mA
<b>Rated operating voltage U<sub>e</sub> DC</b>	24 V
<b>Rated short circuit current</b>	100 A
<b>Ready delay t<sub>v</sub> max.</b>	21 ms
<b>Residual current I<sub>r</sub> max.</b>	30 µA
<b>Ripple max. (% of U<sub>e</sub>)</b>	15 %
<b>Switching frequency</b>	2500 Hz
<b>Utilization category</b>	DC -13
<b>Voltage drop static max.</b>	1.5 V

**Environmental conditions**

<b>Ambient temperature</b>	-25...70 °C
<b>Contamination scale</b>	3
<b>EN 60068-2-27, Shock</b>	Half-sinus, 30 gn, 11 ms
<b>EN 60068-2-6, Vibration</b>	55 Hz, amplitude 1 mm, 3x30 min
<b>Protection degree</b>	IP68

**Functional safety**

<b>MTTF (40 °C)</b>	850 a
---------------------	-------

Inductive Sensors  
**BES 516-329-G-E4-C-05**  
Order Code: BES00T8

# BALLUFF

## Material

Housing material	Brass, Nickel-free coated
Material jacket	PVC
Material sensing surface	LCP
Surface protection	Nickel-free coated

## Mechanical data

Dimension	Ø 12 x 33 mm
Installation	for flush mounting
Size	M12x1
Tightening torque	10 Nm

## Output/Interface

Switching output	NPN normally open (NO)
------------------	------------------------

## Range/Distance

Assured operating distance Sa	3.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	4 mm
Real switching distance sr	4 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

## Remarks

The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

## Wiring Diagrams

