



1) Pressure resistant area



IND. CONT. EQ
 11RZ
 for use in the secondary of
 a class 2 source of supply

Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U_e	1 μ F
Min. operating current I_m	0 mA
No-load current I_o max., damped	16 mA
No-load current I_o max., undamped	9 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	47.0 kOhm
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	200 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Ready delay t_v max.	10 ms
Residual current I_r max.	100 μ A
Ripple max. (% of U_e)	15 %
Switching frequency	200 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

Functional safety

MTTF (40 °C)	375 a
--------------	-------

Inductive Sensors
BES M18EF1-PSC20F-S04G-S
Order Code: BES02Y1



Material

Housing material	Stainless steel
Material sensing surface	Stainless steel

Mechanical data

Dimension	Ø 18 x 63.5 mm
Installation	non-flush
Pressure rating max.	60 bar
Pressure rating, note	Pressure-resistant
Size	M18x1
Tightening torque	50 Nm ±10 %

Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Range/Distance

Assured operating distance Sa	16.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	20 mm
Real switching distance sr	20 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %

Remarks

The sensor is functional again after the overload has been eliminated.
 Installation permitted only in clamp without positive stop.
 When installing in metal see Installation Instructions 939231.
 LED flashes between 100% and approx. 70% of Sr
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

