



IND. CONT. EQ.
 81U2
 Class 2 Type 1

Basic features

Additional features	THA
Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U_e	1 μ F
Min. operating current I_m	0 mA
No-load current I_o max., damped	30 mA
No-load current I_o max., undamped	30 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	2.7 kOhm + D + LED/4.7 kOhm + D
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	130 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Ready delay t_v max.	10 ms
Residual current I_r max.	80 μ A
Ripple max. (% of U_e)	15 %
Switching frequency	500 Hz
Utilization category	DC -13
Voltage drop static max.	3.5 V

Inductive Sensors
BES 517-142-Y-RK
Order Code: **BES02MN**

BALLUFF

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67 only when installed in multiple limit switches

Functional safety

MTTF (40 °C)	1255 a
--------------	--------

Material

Housing material	PA 12
Material sensing surface	PBT

Mechanical data

Connection cross-section	2.5 mm ²
Dimension	60 x 15.5 x 57.9 mm
Installation	for flush mounting
Tightening torque	0.5 Nm

Output/Interface

Switching output	PNP normally open/normally closed (NO/NC)
------------------	---

Range/Distance

Assured operating distance Sa	4 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	5 mm
Real switching distance sr	5 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

Insert element must be installed in aluminum housing.
The sensor is functional again after the overload has been eliminated.
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

