



1) LED function indicator, 2) M5x15 mounting post, 3) Sensing surface



### Basic features

Approval/Conformity	CE EAC WEEE
Basic standard	IEC 60947-5-2

### Display/Operation

Function indicator	yes
Power indicator	no

### Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at $U_e$	0.15 $\mu$ F
Min. operating current $I_m$	0 mA
No-load current $I_o$ max., damped	20 mA
No-load current $I_o$ max., undamped	20 mA
Operating voltage $U_b$	10...30 VDC
Output resistance $R_a$	Open collector
Rated insulation voltage $U_i$	75 V DC
Rated operating current $I_e$	400 mA
Rated operating voltage $U_e$ DC	24 V
Rated short circuit current	100 A
Ripple max. (% of $U_e$ )	15 %
Switching frequency	50 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

### Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP65

### Material

Housing material	Plastic
Material sensing surface	Plastic

## Mechanical data

Dimension	150 x 35 x 35 mm
Installation	non-flush
Tightening torque	3 Nm

## Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

## Range/Distance

Assured operating distance Sa	24 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	30 mm
Real switching distance sr	30 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

## Connector Drawings



## Wiring Diagrams

