



1) Sensing surface



**Basic features**

<b>Approval/Conformity</b>	cULus CE EAC WEEE
<b>Basic standard</b>	IEC 60947-5-2

**Display/Operation**

<b>Function indicator</b>	yes
<b>Power indicator</b>	no

**Electrical connection**

<b>Connection</b>	M5x0.5-Male
<b>Polarity reversal protected</b>	yes
<b>Protection against device mix-ups</b>	yes
<b>Short-circuit protection</b>	yes

**Electrical data**

<b>Load capacitance max. at Ue</b>	0.2 µF
<b>Min. operating current Im</b>	1 mA
<b>No-load current Io max., damped</b>	10 mA
<b>No-load current Io max., undamped</b>	3 mA
<b>Operating voltage Ub</b>	10...30 VDC
<b>Output resistance Ra</b>	Open collector
<b>Rated insulation voltage Ui</b>	75 V DC
<b>Rated operating current Ie</b>	100 mA
<b>Rated operating voltage Ue DC</b>	24 V
<b>Rated short circuit current</b>	100 A
<b>Ready delay tv max.</b>	15 ms
<b>Residual current Ir max.</b>	50 µA
<b>Ripple max. (% of Ue)</b>	10 %
<b>Switching frequency</b>	2000 Hz
<b>Utilization category</b>	DC -13
<b>Voltage drop static max.</b>	3 V

**Environmental conditions**

<b>Ambient temperature</b>	-25...70 °C
<b>Contamination scale</b>	3
<b>EN 60068-2-27, Shock</b>	Half-sinus, 30 gn, 11 ms
<b>EN 60068-2-6, Vibration</b>	55 Hz, amplitude 1 mm, 3x30 min
<b>Protection degree</b>	IP67

**Functional safety**

<b>MTTF (40 °C)</b>	830 a
---------------------	-------

Inductive Sensors  
**BES Q05AC-PSC15B-S26G**  
Order Code: BES01RP

**BALLUFF**

**Material**

Housing material	Stainless steel (1.4305)
Material sensing surface	PBT

**Mechanical data**

Dimension	33 x 5 x 5 mm
Installation	for flush mounting
Size	5x5

**Output/Interface**

Switching output	PNP normally open (NO)
------------------	------------------------

**Range/Distance**

Assured operating distance Sa	1.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	1.5 mm
Real switching distance sr	1.5 mm
Repeat accuracy max. (% of Sr)	10.0 %
Temperature drift max. (% of Sr)	20 %
Tolerance Sr	±10 %

**Remarks**

ESD requirements met if housing is grounded.  
The sensor is functional again after the overload has been eliminated.  
For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

