



Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2
Trademark	Global

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Cable diameter D	3.00 mm
Cable length L	2 m
Conductor cross-section	0.14 mm ²
Connection type	Cable, 2.00 m, PVC
Electrical version	3-wire
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	1.0 µF
No-load current I _o max., damped	2 mA
No-load current I _o max., undamped	7 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	33.0 kOhm
Protection class	II
Rated insulation voltage U _i	250 V AC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	25 ms
Residual current I _r max.	10 µA
Ripple max. (% of U _e)	10 %
Switching frequency	4000 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...70 °C, Temperature drift max. (% of Sr) 15% between 50...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP68

Functional safety

MTTF (40 °C)	595 a
--------------	-------

Inductive Sensors
BES M08EG-POC40F-BV02
Order Code: BES0015



Material

Housing material	Stainless steel
Material jacket	PVC
Material sensing surface	PBT

Mechanical data

Dimension	Ø 8 x 50 mm
Installation	non-flush
Size	M8x1
Tightening torque	8 Nm

Output/Interface

Switching output	PNP normally closed (NC)
------------------	--------------------------

Range/Distance

Assured operating distance Sa	3.2 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	4 mm
Real switching distance sr	4 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

Not for flush mounting: See installation instructions for inductive sensors with extended range 939229.

The sensor is functional again after the overload has been eliminated.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Wiring Diagrams

