



1) Sensing surface, 2) LED green, 3) LED yellow



### Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2

### Display/Operation

Function indicator	yes
Power indicator	yes

### Electrical connection

Cable diameter D	3.80 mm
Cable length L	0.2 m
Connection	M12x1-Male, 4-pin, A-coded
Connection type	Cable with connector, 0.20 m, PUR
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at Ue	1 µF
Min. operating current Im	0 mA
No-load current Io max., damped	15 mA
No-load current Io max., undamped	15 mA
Operating voltage Ub	10...30 VDC
Output resistance Ra	33.0 kOhm + D
Rated insulation voltage Ui	75 V DC
Rated operating current Ie	200 mA
Rated operating voltage Ue DC	24 V
Rated short circuit current	100 A
Ready delay tv max.	20 ms
Residual current Ir max.	80 µA
Ripple max. (% of Ue)	10 %
Switching frequency	150 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

### Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

### Functional safety

MTTF (40 °C)	675 a
--------------	-------

Inductive Sensors  
**BES R01ZC-PAC70B-BP00.2-GS04**  
**Order Code: BES01W2**



**Material**

Housing material	Zinc, Die casting
Material jacket	PUR
Material sensing surface	PA 12

**Mechanical data**

Dimension	32 x 20 x 8 mm
Installation	for flush mounting
Size	32x20x8

**Output/Interface**

Switching output	PNP normally open/normally closed (NO/NC)
------------------	---

**Range/Distance**

Assured operating distance Sa	5.6 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	7 mm
Real switching distance sr	7 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

**Remarks**

The sensor is functional again after the overload has been eliminated.

LED yellow: Function

LED green: Power

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

