



Basic features

Additional features	Factor 1 Weld immune Housing resistant to weld spatter
Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2
Trademark	Factor 1

Display/Operation

Function indicator	yes
Power indicator	no

Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	1 µF
Magnetic field strength, interference field	100 kA/m
Min. operating current I_m	0 mA
No-load current I_o max., damped	33 mA
No-load current I_o max., undamped	25 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	33.0 kOhm + D
Rated insulation voltage U_i	75 V AC
Rated operating current I_e	200 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Ready delay t_v max.	30 ms
Ripple max. (% of U_e)	15 %
Switching frequency	80 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Magnetic field immune	magnetic field immune (AC/DC)
Protection degree	IP67

Functional safety

MTTF (40 °C)	260 a
---------------------	-------

Inductive Sensors
BES M12EI-PSC40A-S04G-S02
Order Code: BES0567



Material

Housing material	Stainless steel, weld spatter resistant, coated
Material sensing surface	Stainless steel, coated
Surface protection	weld spatter resistant coated

Mechanical data

Dimension	Ø 12 x 65 mm
Installation	for flush mounting
Size	M12x1
Tightening torque	15 Nm

Output/Interface

Switching output	PNP normally open (NO)
-------------------------	------------------------

Range/Distance

Assured operating distance Sa	2.9 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	4 mm
Real switching distance sr	4 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■ ■
Temperature drift max. (% of Sr)	15 %
Tolerance Sr	±15 %

Remarks

The sensor is functional again after the overload has been eliminated.
 Installation permitted only in clamp without positive stop.
 Installation notice: flush in Al or non-ferrous metal $Sr = 0.7 \times Sn$
 Use nuts and lockwashers provided.
 For more information about MTTf and B10d see MTTf / B10d Certificate

Indication of the MTTf- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams

