



1) Sensing surface



Basic features

Antenna type	round
Approval/Conformity	CE cULus WEEE
EN 55011	Size 1, Cl. A

Electrical data

Data retention time/years	≥ 10
Memory organization	64 × 8 bits
Programming cycles	Unlimited
Programming time	for 64x8 bits: 1.1s for 1x8 bits: 0.45s
Read cycles	Unlimited
Read time	for 64x8 bits: 0.33 s

Environmental conditions

Ambient temperature	-30...70 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
Protection degree	IP67
Storage temperature	-30...85 °C

Functional Characteristics

Memory type	EEPROM
User data, read/write	8192 Byte

Material

Housing material	Brass, nickel plated
Housing material, surface protection	nickel plated

Mechanical data

Application weight	66.00 g
Dimension	∅ 30 x 35 mm
Installation	metal-free (clear zone) on metal flush in metal
Size	M30x1.5

LF (70/455 kHz)
BIS C-104-32/A
Order Code: BIS0007

BALLUFF

Remarks

Time specification includes data check.
For installation requirements see corresponding read/write head.
Only together with converter BIS C-901 or BIS C-6xx and the appropriate read/write head.
Values are under rated conditions unless otherwise specified.