



Basic features

Approval/Conformity	CE IECEX ATEX WEEE
Basic standard	EN 60079-0 EN 60079-11 IEC 60947-5-6
Ex marking	ATEX: Ex II 1G Ex ia IIC T6 Ga Ex II 1D Ex ia IIIC T145 °C Da IECEX: Ex ia IIC T6 Ga Ex ia IIIC T145 °C Da

Electrical connection

Conductor cross-section	0.34 mm ²
Connection type	Cable, FEP
Polarity reversal protected	no
Short-circuit protection	no

Electrical data

Current consumption max., damped	1 mA
Operating voltage Ub	7.7...9 VDC
Rated insulation voltage Ui	12.6 V DC
Rated operating voltage Ue DC	8.2 V
Rated series resistance Rv	1000 Ohm

Environmental conditions

Ambient temperature	-20...60 °C, depending on Ex category
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP68

Functional safety

MTTF (40 °C)	4110 a
---------------------	--------

Material

Housing material	Stainless steel
Material jacket	FEP
Material sensing surface	PEEK

Mechanical data

Dimension	Ø 12 x 66 mm
Installation	non-flush
Size	M12x1
Tightening torque	10 Nm

Output/Interface

Interface	NAMUR
------------------	-------

Range/Distance

Rated operating distance Sn	4 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Wiring Diagrams

