



1) Sensing surface, 2) Clear zone



Basic features

Antenna type	round
Approval/Conformity	CE cULus WEEE
EN 55011	Size 1, Cl. A

Electrical data

Memory organization	32 × 8 bits
Programming cycles	up to 70 °C: 500,000 up to 30 °C: 1,000,000
Programming time	for 1x8 bits: 0.3s for 32x8 bits: 0.6s
Read cycles	Unlimited
Read time	for 32x8 bits: 0.19 s

Environmental conditions

Ambient temperature	-30...70 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
Protection degree	IP68
Storage temperature	-30...85 °C

Functional Characteristics

Memory type	EEPROM
User data, read/write	1023 Byte

Material

Housing material	PBT
-------------------------	-----

Mechanical data

Application weight	2.00 g
Dimension	∅ 15.5 x 7 mm
Installation	metal-free (clear zone)

Remarks

Only together with converter BIS C-901 or BIS C-6xx and the appropriate read/write head.
 Values are under rated conditions unless otherwise specified.
 For installation requirements see corresponding read/write head.
 Time specification includes data check.
 For installation in metal: Observe clear zone.
 On the last page only 31x8 bits are usable.