



1) Sensing surface, 2) Clear zone



Basic features

Antenna type	round
Approval/Conformity	CE cULus WEEE
EN 55011	Size 1, Cl. A

Electrical connection

Bending radius min., fixed cable	5 x D
Bending radius min., flexible cable	10 x D
Cable diameter D	5.40 mm
Cable length L	1 m, Drag chain compatible
Cable, bending cycles min.	2 million
Connection	M12x1-Female
Connection type	1.00 m, PU

Environmental conditions

Ambient temperature	0...70 °C
Cable temperature, drag chain	-25...60 °C
Cable temperature, fixed routing	-50...80 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
Protection degree	IP67
Storage temperature	-20...85 °C

Functional safety

MTTF (40 °C)	15080 a
---------------------	---------

Material

Housing material	PBT, Blue, Nuts PA 6.6 black
Material jacket	PU

Mechanical data

Application weight	197.00 g
Dimension	Ø 18 x 80 mm
Installation	metal-free (clear zone)
Size	M18x1

LF (70/455 kHz)
BIS C-319-PU1-01
Order Code: BIS0077

BALLUFF

Remarks

Specified relative speed refers to reading/writing the first 4 bytes from the first page.

For installation in metal: Observe clear zone.

Use included plastic nuts for installation.

Time specification includes data check.

Values are under rated conditions unless otherwise specified.

Only together with converter BIS C-901 or BIS C-6xx

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Help Views

