



1) Sensing surface, 2) Tightening torque, 3) see R/W head table



Basic features

Antenna type	round
Approval/Conformity	CE Ecolab WEEE
EN 55011	Size 1, Cl. A
EN 55022	Size 1, Cl. B

Electrical data

Data retention time/years	≥ 10
Memory organization	47 × 16 bytes
Programming cycles	≥ 100.000
Programming time	for 16 bytes: 0.040s
Read cycles	Unlimited
Read time	for 16 bytes: 0.02 s User ID for 4 bytes: 0.02s

Environmental conditions

Ambient temperature	-40...85 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
IP rating per DIN 40050	IPx9K
Protection degree	IP68
Storage temperature temporary	-40...220 °C 1x1000 h, 1500x30 min

Functional Characteristics

Memory type	EEPROM
Supported data carrier types	DIN ISO 14443
UID serial number, read-only	4 Byte
User data, read/write	736 Byte

Functional safety

MTTF (40 °C)	1248 a
--------------	--------

Material

Housing material	PPS
------------------	-----

Mechanical data

Application weight	12.00 g
Dimension	Ø 49.8 x 5.3 mm
Installation	metal-free (clear zone)

HF (13.56 MHz)
BIS M-134-10/L-HT
Order Code: BIS00Y7

BALLUFF

Remarks

The data carrier meets the device protection level EPL Gb and can therefore be used in Zone 1 with Gas Group II. A and II. B.

Values are under rated conditions unless otherwise specified.

Only when used together with the appropriate read/write head.

For installation requirements see corresponding read/write head.

Time specification includes data check.

Storage temperature 1000 h or 1500 cycles à 30 min.

For installation in metal: Observe clear zone.

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.