



### Basic features

Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2

### Display/Operation

Function indicator	yes
Power indicator	no

### Electrical connection

Connection	M12x1-Male, 4-pin, A-coded
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

### Electrical data

Load capacitance max. at $U_e$	1 $\mu$ F
Min. operating current $I_m$	0 mA
No-load current $I_o$ max., damped	10 mA
No-load current $I_o$ max., undamped	10 mA
Operating voltage $U_b$	10...30 VDC
Output resistance $R_a$	47.0 kOhm
Rated insulation voltage $U_i$	75 V DC
Rated operating current $I_e$	200 mA
Rated operating voltage $U_e$ DC	24 V
Rated short circuit current	100 A
Ready delay $t_v$ max.	200 ms
Residual current $I_r$ max.	100 $\mu$ A
Ripple max. (% of $U_e$ )	20 %
Switching frequency	200 Hz
Utilization category	DC -13
Voltage drop static max.	2 V

### Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

### Functional safety

MTTF (40 °C)	390 a
--------------	-------

Inductive Sensors  
**BES M30MI1-PSC22B-S04G**  
**Order Code: BES02YM**



**Material**

Housing material	Brass, Chrome-plated
Material sensing surface	PBT
Surface protection	Chrome-plated

**Mechanical data**

Dimension	Ø 30 x 73.5 mm
Installation	quasi-flush
Size	M30x1.5
Tightening torque	70 Nm

**Output/Interface**

Switching output	PNP normally open (NO)
------------------	------------------------

**Range/Distance**

Assured operating distance Sa	17.6 mm
Hysteresis H max. (% of Sr)	10.0 %
Rated operating distance Sn	22 mm
Real switching distance sr	22 mm
Repeat accuracy max. (% of Sr)	5.0 %
Switching distance marking	■■■
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

**Remarks**

The sensor is functional again after the overload has been eliminated.  
 Quasi-flushed: See installation instructions for inductive sensors with extended range 825356.  
 For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

**Connector Drawings**



**Wiring Diagrams**

