



1) Sensing surface, 2) Clear zone, 3) see corresponding R/W head



Basic features

Antenna type	round
Approval/Conformity	CE WEEE

Electrical data

Data retention time/years	≥ 10
Memory organization	28 × 4 bytes
Programming cycles	up to 50 °C: 100,000
Programming time	for 16 bytes: 0.1s
Read cycles	Unlimited
Read time	User ID for 8 bytes: 0.02 s for 16 bytes: 0.03 s

Environmental conditions

Ambient temperature	0...50 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
Protection degree	IP20
Storage temperature	-20...80 °C

Remarks

Impact loading not permitted.
 Values are under rated conditions unless otherwise specified.
 Only when used together with the appropriate read/write head.
 For installation requirements see corresponding read/write head.
 Time specification includes data check.

Functional Characteristics

Memory type	EEPROM
Supported data carrier types	DIN ISO 15693
UID serial number, read-only	8 Byte
User data, read/write	112 Byte

Material

Housing material	PET, Transparent
-------------------------	------------------

Mechanical data

Application weight	1.00 g
Dimension	1 x 20 x 20 mm
Installation	metal-free (clear zone) on metal