



1) Sensing surface



Basic features

Approval/Conformity	CE EAC WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	no
Power indicator	no

Electrical connection

Cable diameter D	3.5 mm
Cable length L	5 m
Conductor cross-section	0.14 mm ²
Connection type	Cable, 5.0 m, Silicone
Number of conductors	3
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at U _e	9 µF
Min. operating current I _m	0 mA
No-load current I ₀ max., damped	5 mA
No-load current I ₀ max., undamped	3 mA
Operating voltage U _b	10...30 VDC
Rated operating current I _e	120 mA
Rated operating voltage U _e DC	24 V
Ready delay t _v max.	0.5 ms
Residual current I _r max.	2 µA
Ripple max. (% of U _e)	10 %
Switching frequency	500 Hz
Utilization category	DC -13

Environmental conditions

Ambient temperature	-25...130 °C
Protection degree	IP65

Functional safety

MTTF (40 °C)	2869 a
--------------	--------

Material

Housing material	Stainless steel
Material jacket	Silicone
Material sensing surface	LCP

Inductive Sensors
BES Q12EC-PSD40B-ES05
Order Code: BES05N8

BALLUFF

Mechanical data

Dimension	12 x 12 x 59 mm
Installation	for flush mounting
Size	12x12

Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Range/Distance

Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance S _n	4 mm

Wiring Diagrams

