


1) Sensing surface, 2) LED green, 3) LED yellow



Basic features

Approval/Conformity	CE cULus EAC WEEE
Basic standard	IEC 60947-5-2

Display/Operation

Function indicator	yes
Power indicator	yes

Electrical connection

Cable diameter D	3.10 mm
Cable length L	0.3 m
Connection	M8x1-Male, 3-pin
Connection type	Cable with connector, 0.30 m, PUR
Polarity reversal protected	yes
Protection against device mix-ups	yes
Short-circuit protection	yes

Electrical data

Load capacitance max. at Ue	1 µF
Min. operating current I _m	0 mA
No-load current I _o max., damped	15 mA
No-load current I _o max., undamped	8 mA
Operating voltage U _b	10...30 VDC
Output resistance R _a	33.0 kOhm + D
Rated insulation voltage U _i	75 V DC
Rated operating current I _e	200 mA
Rated operating voltage U _e DC	24 V
Rated short circuit current	100 A
Ready delay t _v max.	20 ms
Residual current I _r max.	80 µA
Ripple max. (% of U _e)	10 %
Switching frequency	150 Hz
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...70 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP67

Material

Housing material	Zinc, Die casting
Material jacket	PUR
Material sensing surface	PA 12

Inductive Sensors
BES R01ZC-PSC70B-BP00.3-GS49
Order Code: BES01WF



Mechanical data

Dimension	32 x 20 x 8 mm
Installation	for flush mounting
Size	32x20x8

Output/Interface

Switching output	PNP normally open (NO)
------------------	------------------------

Range/Distance

Assured operating distance Sa	5.6 mm
Hysteresis H max. (% of Sr)	15.0 %
Rated operating distance Sn	7 mm
Real switching distance sr	7 mm
Repeat accuracy max. (% of Sr)	5.0 %
Temperature drift max. (% of Sr)	10 %
Tolerance Sr	±10 %

Remarks

LED yellow: Function
 LED green: Power
 The sensor is functional again after the overload has been eliminated.

Connector Drawings



Wiring Diagrams

