



1) Sensing surface, 2) see remarks, 3) see remarks, 4) see remarks



Basic features

Application	Pneumatic cylinder with T-slot. For dimensions, see sketch in product view.
Approval/Conformity	cULus CE WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Magnetic field sensor
Scope of delivery	Cable clip for T-slot
Trademark	Global

Display/Operation

Function indicator	yes
---------------------------	-----

Electrical connection

Cable	PUR, 0.5 m
Cable diameter D	2.50 mm
Connection	M8x1-Male, 3-pin
Polarity reversal protected	yes
Protection against device mix-ups	no
Short-circuit protection	yes

Electrical data

Assured switching field strength H_a	2 kA/m
Hysteresis H max. (% of H_n)	45 %
Load capacitance max. at U_e	1 μ F
No-load current I_o max., undamped	3 mA
Operating voltage U_b	10...30 VDC
Output resistance R_a	Open drain
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	200 mA
Rated operating voltage U_e DC	24 V
Rated short circuit current	100 A
Rated switch field strength H_n	1.2 kA/m
Residual current I_r max.	80 μ A
Ripple max. (% of U_e)	15 %
Switching frequency	3000 Hz
Turn-off delay t_{off} max.	0.1 ms
Turn-on delay t_{on} max.	0.1 ms
Utilization category	DC -13
Voltage drop static max.	2.5 V

Environmental conditions

Ambient temperature	-25...85 °C
Contamination scale	3
EN 60068-2-27, Shock	Half-sinus, 30 gn, 11 ms
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
ESD	3A(8KV)
Emission	Group 1, Class B
Protection degree	IP67

Functional safety

MTTF (40 °C) 355 a

Material

Housing material PA 12
 Material jacket PUR
 Material sensing surface PU

Mechanical data

Dimension 23.5 x 5 x 5.5 mm
 Mounting can be installed in T-slot from above
 Tightening torque 0.4 Nm

Output/Interface

Switching output PNP normally open (NO)

Range/Distance

Temp. drift max. (% of Hn) 0.3 %

Remarks

- 3) Damping magnet axially magnetized
 Effective operating current I_e with thermally coupled installation in metal.
 - 2) Application area: pneumatic cylinder with t-slot. For dimensions, see sketch in product view.
 - 4) Allen wrench 2.0 mm: max. tightening torque 0.4 Nm. Screw driver 4x0.8 mm: max. tightening torque 1 Nm
- For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



Wiring Diagrams



Help Views

