

1) Fiber clamp, 2) Emitter, 3) Receiver, 4) For DIN rail 35mm, 5) stability, 6) Output function, 7) Sn



IND. CONT. EQ
 77HA
 for use in the secondary of
 a class 2 source of supply



Basic features

Approval/Conformity	cULus CE EAC WEEE
Basic standard	IEC 60947-5-2
Principle of operation	Fiber optic device
Series	75K
Style	Square Straight connection

Electrical connection

Cable diameter D	4.00 mm
Cable length L	2 m
Conductor cross-section	0.14 mm ²
Connection	Cable, 2.00 m, PVC
Fiber optics connection	Ø 2.2 mm
Number of conductors	4
Polarity reversal protected	yes
Short-circuit protection	yes

Display/Operation

Adjuster	button
Display	Output function- LED yellow Stability - LED green
Setting	Factory setting (Reset) Light-on/dark-on Sensitivity (Sn)

Electrical data

Input function	Key disable on/off Same function as button
No-load current I_{o max.} at U_e	20 mA
Operating voltage U_b	10...30 VDC
Protection class	II
Rated insulation voltage U_i	75 V DC
Rated operating current I_e	100 mA
Rated operating voltage U_{e DC}	24 V
Ripple max. (% of U_e)	10 %
Switching frequency	1500 Hz
Turn-off delay t_{off max.}	0.33 ms
Turn-on delay t_{on max.}	0.33 ms
Voltage drop U_{d max.} at I_e	2.4 V

Environmental conditions

Ambient temperature	-20...60 °C
EN 60068-2-6, Vibration	55 Hz, amplitude 1 mm, 3x30 min
Protection degree	IP64

Material

Housing material	ABS
Material jacket	PVC

Remarks

Order accessories separately.
 For additional information, refer to user's guide.
 The sensor is functional again after the overload has been eliminated.
 Do not press key using a pointed tool.

Mechanical data

Dimension	10.4 x 35.4 x 79.3 mm
Mounting	Screw M3 DIN rail 35 mm

Optical features

Ambient light max.	5000 Lux
Light type	LED, red light
Principle of optical operation	depends on fiber optics
Switching function, optical	Light/dark switching
Wave length	660 nm


Output/Interface

Switching output	NPN normally open/normally closed (NO/NC)
-------------------------	---

Range/Distance

Hysteresis H max. (% of S_r)	10.0 %
Range	depends on fiber optics

Wiring Diagrams



Opto Symbols

