



**Basic features**

<b>Application</b>	Pneumatic cylinder with integrated groove
<b>Basic standard</b>	Dimension tolerances: DIN ISO 2768 m
<b>Principle of operation</b>	BMF mounting bracket
<b>Scope of delivery</b>	Fastening screw Mounting bracket Offset screwdriver
<b>Use</b>	for magnetic sensors BMF 303

**Environmental conditions**

<b>Ambient temperature</b>	-40...85 °C
----------------------------	-------------

**Remarks**

for cylinder with closed slot

**Material**

<b>Material</b>	Aluminum
-----------------	----------

**Mechanical data**

<b>Mounting, holder</b>	Threaded pin ISO 4029 M2x3-A2 Offset screwdriver ISO 2936 0.9
<b>Sensor attachment</b>	Threaded pin ISO 4029 M2x3-A2 offset screwdriver ISO 2936 0.9
<b>Size</b>	T-slot
<b>Tightening torque</b>	0.2 Nm
<b>Tightening torque clamping screw</b>	0.2 Nm