



## Basic features

<b>Application</b>	Pneumatic cylinder with integrated groove
<b>Basic standard</b>	Dimension tolerances: DIN ISO 2768 m
<b>Principle of operation</b>	BMF mounting bracket
<b>Scope of delivery</b>	Fastening screw Mounting bracket Offset screwdriver
<b>Use</b>	for magnetic sensors BMF 303

## Environmental conditions

<b>Ambient temperature</b>	-40...85 °C
----------------------------	-------------

## Remarks

US Patent No. 6, 637, 279

## Material

<b>Material</b>	Brass
<b>Surface protection</b>	nickel plated

## Mechanical data

<b>Mounting, holder</b>	Threaded pin ISO 4029 M2x4-A2 Offset screwdriver ISO 2936 0.9
<b>Sensor attachment</b>	Threaded pin ISO 4029 M2x2,5-A2 offset screwdriver ISO 2936 0.9
<b>Size</b>	Slot 10 (Festo)
<b>Tightening torque</b>	0.2 Nm
<b>Tightening torque clamping screw</b>	0.2 Nm

## Help Views

