



Basic features

| | |
|-------------------------------|---|
| Application | Pneumatic cylinder with integrated groove |
| Base type | BMF 305-HW-20 |
| Basic standard | Dimension tolerances: DIN ISO 2768 m |
| Principle of operation | BMF mounting bracket |
| Scope of delivery | Fastening screw Mounting bracket Offset screwdriver |
| Use | for magnetic sensors BMF 305 |

Environmental conditions

| | |
|----------------------------|-------------|
| Ambient temperature | -40...85 °C |
|----------------------------|-------------|

Material

| | |
|---------------------------|---------------|
| Material | Brass |
| Surface protection | nickel plated |

Mechanical data

| | |
|---|---|
| Mounting, holder | Threaded pin ISO 4029 M3x4-A2 Offset screwdriver ISO 2936 1.5 |
| Sensor attachment | Cylinder head screw DIN 7984 M3x6-A2 offset screwdriver ISO 2936 2.0 |
| Size | T-slot |
| Tightening torque | 0.6 Nm |
| Tightening torque clamping screw | 0.5 Nm |

Help Views

