



Basic features

Application	Pneumatic cylinder with integrated groove
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening part Mounting bracket
Use	for magnetic sensors BMF 305

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Mounting, holder	Cylinder head screw DIN 7984 M3x5-A2 Offset screwdriver ISO 2936 2.0
Sensor attachment	Cylinder head screw DIN 7984 M3x5-A2 offset screwdriver ISO 2936 2.0
Size	C-slot (Numatics/Norgren)
Tightening torque	1.5 Nm
Tightening torque clamping screw	1.5 Nm

Help Views

