

Basic features

Approval/Conformity	CE
	EAC
	WEEE
Scope of delivery	Short guide

Display/Operation

IO-Link communication indicator	Green LED
Module supply indicator	Green LED

Electrical connection

Connection (COM 1)	M12x1-Male, 4-pin, A-coded
Connection slots	M12x1-Female, 4-pin, A-coded
Contact, surface protection	nickel plated 2 µm/gold plated 0.4 µm

Electrical data

Burst	3A
Configurable inputs/outputs	no
Current consumption without load, max.	30 mA
ESD	3A
IO-Link function	Device
IO-Link ports, number	1
Operating voltage U_b	18...30.2 VDC
Rated operating voltage U_e DC	24 V

Environmental conditions

Ambient temperature	-5...70 °C
Protection degree	IP67 when threaded in
Storage temperature	-25...70 °C

Functional safety

MTTF (40 °C)	509 a
--------------	-------

Material

Gasket, material	FKM 75
Housing material	PA
Housing shield	no

Mechanical data

Dimension	14.2 x 50.4 x 40 mm
-----------	---------------------

Output/Interface

Analog inputs	Analog, temperature (Pt100)
Cycle time min.	3 ms
IO-Link version	1
Interface	IO-Link 1.0
Process data IN	2 bytes
Process data cycle min.	12 ms
Transfer rate	COM2 (38.4 kBaud)

Range/Distance

Resolution	≤ 14 bits
------------	-----------


Remarks

See short guide

For more information about MTTF and B10d see MTTF / B10d Certificate

Indication of the MTTF- / B10d value does not represent a binding composition and/or life expectancy assurance; these are simply experiential values with no warranty implications. These declared values also do not extend the expiration period for defect claims or affect it in any way.

Connector Drawings



IO-Link

PIN 1: +24V, 1.4A

PIN 2: n.c.

PIN 3: GND, reference potential

PIN 4: C/Q, IO-Link