



1) Sensing surface, 2) Read/write axis, 3) Tightening torque



Basic features

Antenna type	Rod
Approval/Conformity	CE
	WEEE
EN 55022	Size 1, Cl. B

Electrical data

Data retention time/years	≥ 10 at 55 °C
Programming cycles	≥ 10.000.000.000
Programming time	for 16 bytes: 0.006s
Read cycles	Unlimited
Read time	User ID for 8 bytes: 0.02 s for 16 bytes: 0.003 s

Environmental conditions

Ambient temperature	-25...85 °C
Continuous shock load	yes
EN 60068-2-27, Shock	yes
EN 60068-2-32 Free fall	yes
EN 60068-2-6, Vibration	yes
IP rating per DIN 40050	IP68 IPx9K
Storage temperature	-25...85 °C

Functional Characteristics

Memory type	FRAM
Supported data carrier types	DIN ISO 15693 (High Memory)
UID serial number, read-only	8 Byte
User data, read/write	8192 Byte

Material

Housing material	POM
------------------	-----

Mechanical data

Application weight	95.00 g
Dimension	40 x 22 x 80 mm
Installation	metal-free (clear zone) on metal

HF (13.56 MHz)
BIS M-153-11/A
Order Code: BIS011W

BALLUFF

Remarks

Installation type on flat steel
Time specification includes data check.
For installation requirements see corresponding read/write head.
Only when used together with the appropriate read/write head.
Values are under rated conditions unless otherwise specified.
Impact loading not permitted.