



1) Sensing surface, 2) Tightening torque



**Basic features**

<b>Antenna type</b>	Dipole
<b>Approval/Conformity</b>	CE RoHS WEEE
<b>Standards</b>	EPCglobal™ Class 1, Gen 2 ISO 18000-6C

**Electrical data**

<b>Data retention time/years</b>	≥ 50
<b>Polarization</b>	linear
<b>Preferred application</b>	860...930 MHz
<b>Programming cycles</b>	up to 55 °C: 100,000
<b>Read cycles</b>	Unlimited
<b>Working frequency</b>	860...930 MHz

**Environmental conditions**

<b>Ambient temperature</b>	-40...85 °C
<b>EN 60068-2-27, Shock</b>	MIL STD 810-F
<b>Protection degree</b>	IP68
<b>Storage temperature</b>	-40...85 °C

**Functional Characteristics**

<b>EPC memory, read/write</b>	128 Bit
<b>Memory type</b>	EEPROM
<b>TID memory, read-only</b>	96 Bit
<b>User data, read/write</b>	512 Bit

**Material**

<b>Housing material</b>	ABS
-------------------------	-----

**Mechanical data**

<b>Application weight</b>	25.60 g
<b>Dimension</b>	48 x 12.6 x 51 mm
<b>Installation</b>	on metal

**Remarks**

Values are under rated conditions unless otherwise specified.  
 For application on metal