



1) Reference edge, 2) 1st pos., 3) Mark. Safety switch position



Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-4. Switch position: Mechanical
Version	Safety EN 60204-1

Display/Operation

Function indicator	1-4. Switch position: None
--------------------	----------------------------

Electrical connection

Connection type	1-4. Switch position: Screw terminal
-----------------	--------------------------------------

Electrical data

Continuous current	1-4. Switch position: 6 A
Rated operating voltage U _e	1-4. Switch position: 250 V AC
Switching function mechanical	NC forced-opening per VDE Double-interrupting Normally open with snap funct. galvanically isolated One NO and one NC Dual changeover
Switching rate	1-4. Switch position: 160/min

Environmental conditions

Ambient temperature	-5...85 °C
Protection degree	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 85: 1 mil. Switching operations
-----------------------	-------------------------------------

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-4. Switch position: Silver
Plunger material	1-4. Switch position: Stainless steel (1.4034)

Mechanical data

Approach direction	Vertical to mounting surface
Approach speed	1-4. Switch position: 60 m/min
Dimension	100 x 90 x 77 mm
Distance cam - reference edge	1-4. Switch position: 2.50...3.00 mm
Flange, feed-through	1 threaded exit M25
Installation	Horizontal
Life expectancy mechanical	1-4. Switch position: 1 million Switching operations
Number of switching positions	4x Roller
Plunger spacing 1st switch position	50 mm
Plunger style	1-4th switch position: Roller
Switch actuation force	1-4. Switch position: 30 N
Switching element	1-4. Switch position: BSE 85

Range/Distance

Reproducibility
Switch position spacing

1-4. Switch position: ± 0.02 mm
12 mm

Wiring Diagrams

BSE 85

