



Basic features

Application	Pneumatic flat cylinder with integrated groove
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Use	for magnetic sensors BMF 103

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Material

Material	Brass
Surface protection	nickel plated

Mechanical data

Mounting, holder	Threaded pin ISO 4026 M2x3-A2 Offset screwdriver ISO 2936 0.9
Sensor attachment	Cylinder head screw ISO 4762 M2x6-A2 offset screwdriver ISO 2936 1.5
Size	C-slot (SMC/Bimba)
Tightening torque	0.07 Nm
Tightening torque clamping screw	0.2 Nm

Help Views

