

Basic features

Application	Pneumatic cylinder with integrated groove Holder suitable for 2 T slot dimension.
Basic standard	Dimension tolerances: DIN ISO 2768 m
Principle of operation	BMF mounting bracket
Scope of delivery	Fastening screw Mounting bracket Offset screwdriver
Use	for magnetic sensors BMF 303

Environmental conditions

Ambient temperature	-40...85 °C
----------------------------	-------------

Remarks

US Patent No. 6, 637, 279








Material

Material	Aluminum
Surface protection	Anodized

Mechanical data

Mounting, holder	Threaded pin ISO 4029 M2x5-A2 Offset screwdriver ISO 2936 0.9
Sensor attachment	Threaded pin ISO 4029 M2x2,5-A2 offset screwdriver ISO 2936 0.9
Size	T-slot (SMC)
Tightening torque	0.2 Nm
Tightening torque clamping screw	0.2 Nm

Help Views



- 1) Slot A
- 2) Slot B