



### Basic features

|                               |                                           |
|-------------------------------|-------------------------------------------|
| <b>Application</b>            | Pneumatic cylinder with integrated groove |
| <b>Basic standard</b>         | Dimension tolerances: DIN ISO 2768 m      |
| <b>Principle of operation</b> | BMF mounting bracket                      |
| <b>Scope of delivery</b>      | Fastening part<br>Mounting bracket        |
| <b>Use</b>                    | for magnetic sensors BMF 305              |

### Environmental conditions

|                            |             |
|----------------------------|-------------|
| <b>Ambient temperature</b> | -40...85 °C |
|----------------------------|-------------|

### Material

|                           |          |
|---------------------------|----------|
| <b>Material</b>           | Aluminum |
| <b>Surface protection</b> | Anodized |

### Mechanical data

|                          |                                                                                   |
|--------------------------|-----------------------------------------------------------------------------------|
| <b>Sensor attachment</b> | Cylinder head screw DIN 7984<br>M3x10-A2 cylinder head screw<br>ISO 1207 M3x10-A2 |
| <b>Size</b>              | T-slot                                                                            |
| <b>Tightening torque</b> | 1.5 Nm                                                                            |

### Help Views

