

1) Reference edge



Basic features

Approval/Conformity	CE WEEE
Basic standard	IEC 60947-5-1
Operating principle	1-3. Switch position: Mechanical
Version	Snap contact

Display/Operation

Function indicator	1-3. Switch position: None
---------------------------	----------------------------

Electrical connection

Connection	M12x1-Flange male, 5-pin
Connection type	1. Switch position: Connector

Electrical data

Continuous current	1-3. Switch position: 4 A
Rated operating voltage Ue	1-3. Switch position: 250 V AC
Switching rate	1-3. Switch position: 200/min

Environmental conditions

Ambient temperature	-5...85 °C
Protection degree	IP67

Functional safety

B10d (EN ISO 13849-1)	BSE 70.1: 10 mil. Switching operations
------------------------------	--

Material

Housing material	Aluminum, Anodized
Housing material, surface protection	Anodized
Material contacts	1-3. Switch position: Silver
Plunger material	1-3. Switch position: Stainless steel (1.4034)


Mechanical data

Approach direction	longitudinal, parallel to attachment surface
Approach speed	1-3. Switch position: 20 m/min
Distance cam - reference edge	1-3. Switch position: 2.30...2.80 mm
Flange, feed-through	None
Installation	Vertical
Life expectancy mechanical	1-3. Switch position: 10 million Switching operations
Number of switching positions	3x Chisel
Plunger style	1-3rd switch position: Chisel
Switch actuation force	1-3. Switch position: 8 N
Switching element	1-3. Switch position: BSE 70.1

Range/Distance

Reproducibility	1-3. Switch position: ±0.02 mm
------------------------	--------------------------------

Connector Drawings



View of connector side

Wiring Diagrams

